

## YAV162M4

by Burndy  
Catalog ID: YAV162M4

HYLUG™ Copper tubing Compression terminals, 16 mm<sup>2</sup>, M4 Stud, 2 Holes, Tin Plated



### Product Details

#### General

Die Index	7
Material	Copper
Plated	YES
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637609
UPC 12 Digit	7818106376099

#### Dimensions

Dimension - B Length inch	.5 in
Dimension - Hole Size inch	0.18 in
Dimension - Hole Size mm	4.6 mm
Dimension - L Length Overall mm	76.1 mm
Dimension - Length Overall inch	3.00 in
Dimension - Pad Width inch	12.2 in
Dimension - Strip Length inch	0.51 in
Dimension - Z inch	0.23 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	50
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)