

YAV162M8

by Burndy
Catalog ID: YAV162M8

HYLUG™ Copper tubing Compression terminals,16 mm²,M8 Stud, 2 Holes,Tin Plated



Product Details

General

Die Index	7
Material	Copper
Plated	YES
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637630
UPC 12 Digit	7818106376300

Dimensions

Dimension - B Length inch	.5 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8.4 mm
Dimension - L Length Overall mm	82.5 mm
Dimension - Length Overall inch	3.25 in
Dimension - Pad Width inch	15.2 in
Dimension - Strip Length inch	0.51 in
Dimension - Z inch	0.36 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)