

YAV1852M12

by Burndy
Catalog ID: YAV1852M12

Non Insul Cu Comp Tubular Terminal, Metric, 2 Hole/W/InspWindow, 185 mm, M12 Stud, 1.75" Spacing, Tin - Electro Plated, 18 Index



Product Details

General

Connector Type	Terminal
Die Index	18
Material	Copper
Physical Attribute - Number of Holes	2
Plated	YES
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442746
UPC 12 Digit	7818104427466

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	114.6 mm
Dimension - Length Overall inch	4.51 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	32.8 in
Dimension - Strip Length inch	1.14 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	350
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)