

# YAV185F2M10

by Burndy  
Catalog ID: YAV185F2M10

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 185 mm, M10 Stud, 44.5 mm Spacing, Standard Barrel, 29 mm Wire Strip Length



## Product Details

### General

|              |                      |
|--------------|----------------------|
| Die Index    | 18                   |
| Material     | Copper               |
| Plated       | YES                  |
| Plating Type | Tin - Electro Plated |
| Trade Name   | HYLUG™               |
| Type         | Metric Terminals     |
| UPC          | 781810640944         |
| UPC 12 Digit | 7818106409444        |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - B Length inch       | 1.19 in  |
| Dimension - Hole Size inch      | 0.41 in  |
| Dimension - Hole Size mm        | 10.4 mm  |
| Dimension - L Length Overall mm | 112.8 mm |
| Dimension - Length Overall inch | 4.44 in  |
| Dimension - Pad Width inch      | 1.40 in  |
| Dimension - Strip Length inch   | 1.14 in  |
| Dimension - Z inch              | 0.42 in  |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

### Conductor Related

|                                   |     |
|-----------------------------------|-----|
| Conductor - Copper DLO Size Range | N/A |
|-----------------------------------|-----|

## Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | CM |

## Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)