

# YAV185M8

by Burndy  
Catalog ID: YAV185M8

Compression terminal HYLUG™ Copper tubing, 1 Hole, 185 mm, M8 Stud, Tin Plating



## Product Details

### General

Die Index	18
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637524
UPC 12 Digit	7818106375244

### Dimensions

Dimension - B Length inch	1.06 in
Dimension - Hole Size mm	8.4 mm
Dimension - L Length Overall mm	60.2 mm
Dimension - Length Overall inch	2.37 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1.14 in
Dimension - Z inch	0.36 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)