



YAV18H21FBOX

by Burndy
Catalog ID: YAV18H21FBOX

Uninsulated Compression Terminal Fork Tongue With Shroud Seamless ,
22-18 AWG, #8 -#10 Stud, .97 in L, Tin Plated.

Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810021668
UPC 12 Digit	7818100216688

Dimensions

Cable Insulation Diameter Maximum	0.120 in
Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.97 in
Dimension - N inch	0.22 in
Dimension - Outside Diameter inch	0.13 in
Dimension - Pad Width inch	0.37 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.22 in

Conductor Related

Conductor - Copper Solid Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Solid Size Range	22 AWG-18 AWG

Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)