

YAV18T19FBOX

by Burndy
Catalog ID: YAV18T19FBOX

Prop 65 Notice

Seamless Uninsulated Fork Tongue Terminal, 22-18, 4-6, .80 in L.

Features: The Type YAV-T-F HYLUG Is A Seamless Heavy Duty Uninsulated Compression Fork tongue Terminal Manufactured From Electro -Lytic Copper For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, The Seamless Design Produces A Double Thick Tongue And The Seamless Barrel Provides A Strong Highly Reliable Connection, All The Benefits Of The Type YAV Apply For The Same Wire Sizes, Fork Tongue: Allows Installation Of Compression Terminal Under Screw Head Without Complete Removal Of The Screw, Installation Tool: Non-Ratchet: Y10D, Y1022 Tool, Ratchet: MR8-G98, MR8-9Q, Y8MRB-1, MR20 Tool, Package: Box, Wire Shroud: No, Conductor Type: Commercial/Military Stranded Copper, Wire Strip Length: 9/32 IN, Finish: Electro-Tin Plated, Tongue Angle: Straight



Product Details

General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Terminal - Fork
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810533987
UPC 12 Digit	7818105339877

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - D inch	0.50 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.84 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in

Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.25 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)