



YAV18T4BOX

by Burndy
Catalog ID: YAV18T4BOX

Prop 65 Notice

Uninsulated Cu Compression Terminal, Ring Tongue, #22 - #18 AN, #3- #4 stud

Product Details

General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810533925

Dimensions

Dimension - B Length fraction	17/81 in
Dimension - B Length inch	0.21 in
Dimension - D inch	0.26 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in
Dimension - N inch	0.09 in
Dimension - Outside Diameter inch	0.13 in
Dimension - Pad Width inch	0.19 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#3;#4
Dimension - Z inch	0.16 in

Conductor Related

Conductor - Copper Solid Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Solid Size Range	22 AWG-18 AWG
Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Navy Size	1 (1);1 (7);1 (10);1 1/2 (1);1 1/2 (7);1 1/2 (16);1 1/2 (41);2 (7)
Conductor - Copper Str Navy Size Range	1 (1)-2 (7)

Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)