



YAV1C2TC38FXB

by Burndy
Catalog ID: YAV1C2TC38FXB

Two Hole Long barrel Cu Compression terminal with Belled End, Without Inspection Window , #1 AWG Flex, 3/8" stud

Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810057056
UPC 12 Digit	7818100570566

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.83 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.74 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	3/8

Dimension - Thread Size	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper DLO Size Range	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex G Size Range	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex H Size Range	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex I Size Range	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex K Size Range	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Flex M Size Range	1 AWG
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)