

## YAV1CL1NK

by Burndy  
Catalog ID: YAV1CL1NK

Prop 65 Notice

Cu Tubing Compression Ring Tongue Terminal, 1 Hole W/InspWindow, AN-1, 1/4" Stud, Uninsulated, Nickel Plated



## Product Details

### General

Connector Type	Terminal
Die Index	42
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810044872
UPC 12 Digit	7818100448722

### Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.76 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	47 mm
Dimension - Length Overall inch	1.84 in
Dimension - N inch	0.38 in

Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	5/8
Dimension - Z inch	0.38 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	200
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)