

# YAV1CL2NT14FX

by Burndy  
Catalog ID: YAV1CL2NT14FX

Prop 65 Notice

Copper Compression Lug, Narrow Tongue, 2 Holes W/ Inspection Window, 1 AWG, 75 Navy, 1/4" Stud, 11 index, Green Tin Plated.



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	11
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810234631

### Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	1.28 in
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.28 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper DLO Size Range	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex G Size Range	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex H Size Range	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex I Size Range	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex K Size Range	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Flex M Size Range	1 AWG
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - CopperWeld Str Size	1 F AWG;1 G AWG;1 J AWG;1 K AWG;1 N AWG
Conductor - CopperWeld Str Size Range	1 F AWG-1 N AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)