



YAV1CL4NK

by Burndy
Catalog ID: YAV1CL4NK

Seamless Uninsulated Compression Heavy Duty Ring Tongue Terminal
#22-10 Stranded and Solid Copper, Nickel plate

Product Details

General

Connector Type	Terminal
Die Index	42
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel
Temperature Rating	194
Type	Standard Barrel, Nickel Plated
UPC	781810504291
UPC 12 Digit	7818105042911

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Bolt Hole Size inch	0.45 in
Dimension - D inch	0.89 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - N inch	0.43 in
Dimension - Pad Width inch	0.86 in
Dimension - Z inch	0.46 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Aircraft Size	AN 1
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)