



YAV1CTC516FXB

by Burndy
Catalog ID: YAV1CTC516FXB

Prop 65 Notice

HYLUG™ Copper tubing Compression terminals, 1AwG , 75 Navy, M8 Stud,
1 Holes, Tin Plated

Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810095232
UPC 12 Digit	7818100952322

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.60 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1.50 in
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)