

## YAV1T38B

by Burndy  
Catalog ID: YAV1T38B

Prop 65 Notice

Copper Compression Lug, 1 Hole ,1 Flex, 3/8" Stud, Short Barrel, Belled End, Tin Plated



## Product Details

### General

Color Code	Black
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	621945082274
UPC 12 Digit	6219450822744

### Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.80 in
Dimension - N inch	0.40 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	0.68 in
Dimension - Z inch	0.46 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	10
-----------------------	----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)