

YAV2402M10

by Burndy
Catalog ID: YAV2402M10

HYLUG™ Copper tubing Compression terminals, 240 mm², M10 Stud, 2 Holes, Tin Plated



Product Details

General

Die Index	20
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638125
UPC 12 Digit	7818106381255

Dimensions

Dimension - B Length inch	32.3 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - L Length Overall mm	117.6 mm
Dimension - Length Overall inch	4.63 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Z inch	0.42 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)