

YAV2402M16

by Burndy
Catalog ID: YAV2402M16

Copper Tubing Terminal, 2 Hole W/insp window, 240 mm Class 2, 20 Index, 16 mm Stud



Product Details

General

Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442777
UPC 12 Digit	781810442777

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	130.3 mm
Dimension - Length Overall inch	5.13 in
Dimension - Pad Width inch	39.4 in
Dimension - Strip Length inch	1.30 in
Dimension - Z inch	0.67 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)