

YAV2402M20

by Burndy
Catalog ID: YAV2402M20

Hylug Copper tubing Compression terminals, 240 mm², M20 Stud, 2 Holes, Tin Plated



Product Details

General

Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638132
UPC 12 Digit	7818106381322

Dimensions

Dimension - B Length inch	32.3 in
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	141 mm
Dimension - Length Overall inch	5.61 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Z inch	0.89 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status

CM

Logistics

Minimum Pack Quantity

5

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)