

## YAV240F2M12

by Burndy  
Catalog ID: YAV240F2M12

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 240 mm, M12 Stud, 44.5 mm Spacing, Standard Barrel, 33 mm Wire Strip Length



### Product Details

#### General

Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641002
UPC 12 Digit	7818106410022

#### Dimensions

Dimension - B Length inch	1.27 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	124 mm
Dimension - Length Overall inch	4.88 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Z inch	0.55 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)