

YAV240F2M20

by Burndy
Catalog ID: YAV240F2M20

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 240 mm, M20 Stud, 44.5 mm Spacing, Standard Barrel, 33 mm Wire Strip Length



Product Details

General

Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641033
UPC 12 Digit	7818106410333

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	141.3 mm
Dimension - Length Overall inch	5.56 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Z inch	0.89 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)