

YAV240FM10

by Burndy
Catalog ID: YAV240FM10

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 240 mm, 10 mm Stud, 2.87 IN L, Compression, 20 Index, 33 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322376
UPC 12 Digit	7818103223766

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	72.9 mm
Dimension - Length Overall inch	2.87 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	240
Conductor - Copper Flex H Size	240
Conductor - Copper Flex I Size	240
Conductor - Copper Flex K Size	240
Conductor - Copper Flex M Size	240

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)