

YAV240FM14

by Burndy
Catalog ID: YAV240FM14

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 240 mm, 14 mm Stud, 3.16 IN L, Compression, 20 Index, 33 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322390
UPC 12 Digit	7818103223900

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Hole Size inch	0.59 in
Dimension - Hole Size mm	15 mm
Dimension - L Length Overall mm	80.2 mm
Dimension - Length Overall inch	3.16 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Standards - RoHS Compliance Status

CM

Logistics

Minimum Pack Quantity

5

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)