

YAV240M12

by Burndy
Catalog ID: YAV240M12

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W, 240mm Class2, 1/2" stud, Tin - Electro Plated, 20 Index



Product Details

General

Connector Type	Terminal
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810285749
UPC 12 Digit	7818102857499

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - D inch	1.14 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	80.2 mm
Dimension - Length Overall inch	3.16 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Size	500
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)