

YAV240M20

by Burndy
Catalog ID: YAV240M20

Copper Tubing Terminal, 1 Hole W/insp window, 240 mm Class 2, 20 Index, 20 mm Stud



Product Details

General

Connector Type	Terminal
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322468
UPC 12 Digit	7818103224688

Dimensions

Dimension - B Length inch	1.27 in
Dimension - D inch	1.72 in
Dimension - Hole Size inch	0.94 in
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	96.6 mm
Dimension - Length Overall inch	3.80 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)