

## YAV252M6

by Burndy  
Catalog ID: YAV252M6

Hylug Copper tubing Compression terminals, 25 mm<sup>2</sup>, M6 Stud, 2 Holes, Tin Plated



### Product Details

#### General

Die Index	9
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637777
UPC 12 Digit	7818106377777

#### Dimensions

Dimension - B Length inch	12.7 in
Dimension - Hole Size mm	0.27 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.20 in
Dimension - Pad Width inch	12.7 in
Dimension - Strip Length inch	0.51 in
Dimension - Z inch	0.33 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

50
----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)