

# YAV252TC38FXB

by Burndy  
Catalog ID: YAV252TC38FXB

Prop 65 Notice

Two Hole Long barrel Cu Compression terminal with Belled End, Without Inspection Window , 1/0 Flex AWG, 3/8" stud



## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	12
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810065525
UPC 12 Digit	7818100655255

### Dimensions

Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.83 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.53 in
Dimension - N inch	0.41 in

Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24) DLO
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Flex M Size Range	1/0 AWG
Conductor - Copper Str Size	1/0
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	25
-----------------------	----

## For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)