



YAV25L1NK

by Burndy
Catalog ID: YAV25L1NK

Prop 65 Notice

Copper Tubing Terminal, 1/4 IN Stud, 43 Index

Product Details

General

Connector Type	Terminal
Die Index	43
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810069721
UPC 12 Digit	7818100697211

Dimensions

Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.85 in
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.03 in
Dimension - N inch	0.42 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Z inch	0.43 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Aircraft Size	0 Aircraft
Conductor - Copper Str Aircraft Size Range	0 Aircraft
Conductor - Material	Copper
Conductor Type	CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)