



YAV25LNT14FX

by Burndy
Catalog ID: YAV25LNT14FX

Prop 65 Notice

Cu compression narrow Tongue std barrel-Flex conductor, Single hole W/ insp window, 1/0 AWG, 1/4" stud, Pink, 12 index

Product Details

General

| | |
|--------------------------------------|----------------------|
| Color Code | Pink |
| Connector Type | Terminal |
| Die Index | 12 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| UPC | 781810457245 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 11/16 in |
| Dimension - B Length inch | 0.69 in |
| Dimension - Bolt Hole Size inch | 0.27 in |
| Dimension - D inch | 0.63 in |
| Dimension - L Length Overall mm | 44 mm |
| Dimension - Length Overall inch | 1.75 in |
| Dimension - N inch | 0.31 in |
| Dimension - Outside Diameter inch | 0.56 in |
| Dimension - Pad Width inch | 0.67 in |
| Dimension - Strip Length inch | 11/16 |
| Dimension - Stud Size inch | 1/4 |
| Dimension - Z inch | 0.32 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--------------------------------------|-------------------|
| Conductor - Copper DLO Size | 1/0 (275/#24) DLO |
| Conductor - Copper DLO Size Range | 1/0 (275/#24) DLO |
| Conductor - Copper Flex G Size | 1/0 AWG |
| Conductor - Copper Flex G Size Range | 1/0 AWG |
| Conductor - Copper Flex H Size | 1/0 AWG |
| Conductor - Copper Flex H Size Range | 1/0 AWG |
| Conductor - Copper Flex I Size | 1/0 AWG |
| Conductor - Copper Flex I Size Range | 1/0 AWG |
| Conductor - Copper Flex K Size | 1/0 AWG |
| Conductor - Copper Flex K Size Range | 1/0 AWG |
| Conductor - Copper Flex M Size | 1/0 AWG |
| Conductor - Copper Flex M Size Range | 1/0 AWG |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)