

YAV25M10

by Burndy
Catalog ID: YAV25M10

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W, 25 mm Class 2, 3/8" stud, Tin - Electro Plated, 9 Index, Tongue Thickness :2.0

Features:Electolytic copper Tube, Electro tin plate.



Product Details

General

Application	For Use On: Metric Conductor with Window Lug
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Yes
Plating Type	Tin - Electro Plated
Sub Brand	Terminals, HYLUG
Trade Name	HYLUG™
Type	YAV
UPC	781810373330
UPC 12 Digit	7818103733300

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	41.4 mm
Dimension - Length Overall inch	1.63 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	0.50 in
Dimension - Stud Size inch	M10
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	4 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)