

YAV25M12

by Burndy
Catalog ID: YAV25M12

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W, 25 mm Class 2, 3/8" stud, Tin - Electro Plated, 9 Index, Tongue Thickness :1.5



Product Details

General

Connector Type	Terminal
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810124239
UPC 12 Digit	7818101242399

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13.2mm
Dimension - L Length Overall mm	42.7 mm
Dimension - Length Overall inch	1.68 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.73 in
Dimension - Strip Length inch	0.50 in
Dimension - Stud Size inch	#12
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	4 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)