

YAV26L1NK

by Burndy
Catalog ID: YAV26L1NK

Prop 65 Notice

Cu tubing Compression Terminal, 1 Hole W/InspWindow, AN-2/O, 1/4" Stud, Nickel Plated



Product Details

General

| | |
|--------------------------------------|--------------------------------|
| Connector Type | Terminal |
| Die Index | 44 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Yes |
| Plating Type | Nickel |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Nickel Plated |
| UPC | 781810069844 |
| UPC 12 Digit | 7818100698444 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 0.782 in |
| Dimension - Length Overall inch | 2.319 in |
| Dimension - N inch | 0.467 in |
| Dimension - Pad Width inch | 0.934 in |
| Dimension - Strip Length inch | 13/16 in |
| Dimension - Z inch | 0.48 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

Conductor Related

| | |
|--------------------------------------|--------|
| Conductor - Copper Str Aircraft Size | AN 00 |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)