

YAV26L2NK

by Burndy
Catalog ID: YAV26L2NK

Prop 65 Notice

Cu Tubing Hylug, 1 Hole with Inspection Window, AN-2/O Aircraft, 600V-35kV, 5/16" stud, Seamless, Compression



Product Details

General

Connector Type	Terminal
Die Index	44
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Nickel
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810139714
UPC 12 Digit	7818101397144

Dimensions

Dimension - B Length inch	0.782 in
Dimension - Length Overall inch	2.319 in
Dimension - N inch	0.467 in
Dimension - Pad Width inch	0.934 in
Dimension - Strip Length inch	13/16 in
Dimension - Z inch	0.48 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Aircraft Size	00 Aircraft
Conductor - Material	Copper
Conductor Type	CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)