

# YAV26L2NT516FX

by Burndy  
Catalog ID: YAV26L2NT516FX

Prop 65 Notice

Copper Compression Lug, Narrow Tongue, 2 Holes W/ Inspection Window, 2/0 AWG, 5/16" Stud, 13 index, Black, Tin plated



## Product Details

### General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810498057

### Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Diameter Min Size inch	1.71 in
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	2.99 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.37 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	2/0 (375/#24)
Conductor - Copper Flex G Size	2/0
Conductor - Copper Flex H Size	2/0
Conductor - Copper Flex I Size	2/0
Conductor - Copper Flex K Size	2/0
Conductor - Copper Flex M Size	2/0
Conductor - Copper Str Size	2/0 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)