



## YAV26L31

by Burndy  
Catalog ID: YAV26L31

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole W/ Inspection Window, AN- 2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated

### Product Details

#### General

Connector Type	Terminal
Die Index	44
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> <li>DLP Copper</li> <li>Tin Plating</li> </ul>
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810088975

#### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	2.10 in
Dimension - N inch	0.39 in
Dimension - Pad Width inch	0.93 in
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

#### Conductor Related

Conductor - Copper Str Aircraft Size	AN-2/0
Conductor Type	<ul style="list-style-type: none"> <li>CU C Solid-Size</li> <li>CU C Str-Size</li> </ul>

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)