



YAV26RS

by Burndy
Catalog ID: YAV26RS

Copper Compression Right Angled Lug, Heavy Duty, 1 Hole w/ Inspection Hole, AN-2/O Flex, 3/8" Stud, Short Barrel, Tin Plated.

Features: Factory Formed Right Angle HYLUG Connectors Made Of Seamless Pure Copper Tubing, These Rugged Terminals Withstand The Most Severe Applications, Inspection Hole In Barrel Permits Visual Check Of Wire Insertion, Tin Plated To Resist Corrosion, Meets Requirements Of SAE-AS7928, Wire Shroud: No, Package: Bulk, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: Y29NC, Y29BH Tool, DV26L Die Nest, Y29PR Die Indentor, Wire Strip Length: 13/16 IN, Conductor Type: Commercial/Military Stranded Copper, Tongue Angle: 90 DEG, Finish: Electro-Tin Plated

Product Details

General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Terminal
Die Index	44
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025871

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - G inch	1.44 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.58 in
Dimension - N inch	0.39 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	0.92 in
Dimension - Strip Length inch	13/16

Dimension - Stud Size inch	3/8
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 00
Conductor - Copper Str Size	2/0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)