



YAV27L15BOX

by Burndy
Catalog ID: YAV27L15BOX

Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Hole, AN-3/0 Flex, 5/8" Stud, 2.60 IN L, 1.03 IN W, Short Barrel, Tin Plated

Product Details

General

| | |
|--------------------------------------|---|
| Connector Type | Terminal |
| Die Index | 45 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Material Composition | <ul style="list-style-type: none"> DLP Copper Tin Plating |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Ring Tongue |
| UPC | 781810540503 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 3/4 in |
| Dimension - B Length inch | 0.78 in |
| Dimension - Bolt Hole Size inch | 0.66 in |
| Dimension - Hole Size mm | 17 mm |
| Dimension - Length Overall inch | 2.60 in |
| Dimension - N inch | 0.56 in |
| Dimension - Pad Width inch | 1.03 in |
| Dimension - Strip Length inch | 13/16 in |
| Dimension - Stud Size inch | 5/8 |
| Dimension - Z inch | 0.62 in |
| Physical Attribute - Tongue Angle | Straight |

Conductor Related

| | |
|--------------------------------------|---------|
| Conductor - Copper Str Aircraft Size | AN 000 |
| Conductor - Copper Str Size | 3/0 AWG |

| | |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |
|----------------|---|

Certifications and Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)