

YAV27L42NK

by Burndy
Catalog ID: YAV27L42NK

Prop 65 Notice

Cu Tubing HYLUG™; 1 Hole with Inspection Window; AN-3/0 Aircraft; 3/8" stud; Seamless; Compression



Product Details

General

Connector Type	Terminal
Die Index	45
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel Plated
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810069899
UPC 12 Digit	7818100698999

Dimensions

Dimension - B Length inch	0.782 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	2.454 in
Dimension - N inch	0.415 in
Dimension - Pad Width inch	0.826 in
Dimension - Z inch	0.52 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Aircraft Size	000 Aircraft
Conductor - Copper Str Aircraft Size Range	000 Aircraft
Conductor - Material	Copper
Conductor Type	CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)