



YAV27RSNK

by Burndy
Catalog ID: YAV27RSNK

Prop 65 Notice

Heavy Duty Right-Angled Terminal, 3/0 AWG, 3/8" stud, 1 Hole, 90 Degree Bent, Nickel Plated

Product Details

General

Connector Type	Terminal
Die Index	45
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Standard Barrel, Military Specification
UPC	781810219010
UPC 12 Digit	7818102190100

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - G inch	1.47 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.61 in
Dimension - N inch	0.48 in

Dimension - Outside Diameter inch	0.71 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	7/8
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Aircraft Size	AN 000
Conductor - Copper Str Aircraft Size Range	AN 000
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)