



## YAV28L12BR

by Burndy  
Catalog ID: YAV28L12BR

Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Hole, AN-4/0 Flex, 1/2" Stud, Short Barrel, Unplated

### Product Details

#### General

Connector Type	Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810083222

#### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size mm	13 mm
Dimension - Length Overall inch	2.72 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.12 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	1/2 in
Dimension - Z inch	0.60 in
Physical Attribute - Tongue Angle	Straight

#### Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)