

YAV28L12B

by Burndy
Catalog ID: YAV28L12B

Cu Compression Ring Terminal, 1 Hole W/InspWindow, AN-4/O, Belled End



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	781810428412
UPC 12 Digit	7818104284122

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	0.97 in
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.47 in
Dimension - N inch	0.48 in

Dimension - Outside Diameter inch	0.72 in
Dimension - Pad Width inch	1.14 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.48 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Aircraft Size	AN 0000
Conductor - Copper Str Aircraft Size Range	AN 0000
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)