

YAV28L14NK

by Burndy
Catalog ID: YAV28L14NK

Cu tubing Compression Terminal, 1 Hole W/InspWindow, AN-4/O, 3/4"
Stud, Nickel Plated



Product Details

General

Connector Type	Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810044865
UPC 12 Digit	7818100448655

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - D inch	1.40 in
Dimension - Hole Size inch	0.78 in
Dimension - Hole Size mm	20 mm
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.95 in

Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.23 in
Dimension - Strip Length inch	7/8
Dimension - Thread Size	3/4 in
Dimension - Z inch	0.78 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Aircraft Size	AN 0000
Conductor - Copper Str Aircraft Size Range	AN 0000
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)