



YAV28L54NK

by Burndy
Catalog ID: YAV28L54NK

Heavy Duty Right-Angle Terminals.

Product Details

General

| | |
|--------------------------------------|---------------|
| Connector Type | Terminal |
| Die Index | 46 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Ring Tongue |
| UPC | 781810216477 |
| UPC 12 Digit | 7818102164777 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 7/8 in |
| Dimension - B Length inch | 0.85 in |
| Dimension - Bolt Hole Size inch | 0.91 in |
| Dimension - Bolt Size fraction | 7/8 |
| Dimension - D inch | 1.40 in |
| Dimension - Hole Size inch | 0.90 in |
| Dimension - Hole Size mm | 23 mm |
| Dimension - Length Overall inch | 2.95 in |
| Dimension - N inch | 0.62 in |
| Dimension - Pad Width inch | 1.23 in |
| Dimension - Thread Size | 7/8 in |
| Dimension - Z inch | 0.78 in |
| Physical Attribute - Tongue Angle | Straight |

Conductor Related

| | |
|--------------------------------------|---------|
| Conductor - Copper Str Aircraft Size | AN 0000 |
|--------------------------------------|---------|

| | |
|----------------|-------------------------------------------------------------------------------------------|
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |
|----------------|-------------------------------------------------------------------------------------------|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)