



YAV28L56NK

by Burndy
Catalog ID: YAV28L56NK

Prop 65 Notice

Heavy Duty Right-AngleTerminals.

Product Details

General

Connector Type	Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810216484
UPC 12 Digit	7818102164844

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	1.16 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - Length Overall inch	2.72 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.12 in
Dimension - Thread Size	5/16 in
Dimension - Z inch	0.60 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 0000
--------------------------------------	---------

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)