



YAV28RS

by Burndy
Catalog ID: YAV28RS

Copper Compression Right Angled Lug, Heavy Duty, 1 Hole w/ Inspection Hole, AN-4/0 Flex, 3/8" Stud, Short Barrel, Tin Plated.

Features: Tin plated to resist corrosion, seamless pure copper tubing.

Product Details

General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025895

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - G inch	1.54 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - N inch	0.48 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Pad Width inch	1.12 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor - Copper Str Size	4/0
Conductor - Copper Str Size Range	4/0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)