

# YAV2C2NT38FXB

by Burndy  
Catalog ID: YAV2C2NT38FXB

Prop 65 Notice

Narrow Tongue Terminal, 2 Hole, #2 AWG Code, 3/8" Stud, Belled End



## Product Details

### General

Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810278185
UPC 12 Digit	7818102781855

### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.35 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	91 mm
Dimension - Length Overall inch	3.57 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.46 in
Dimension - P inch	1.65 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	3 (125/#24) DLO;2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)