



YAV2CL1NK

by Burndy
Catalog ID: YAV2CL1NK

Prop 65 Notice

Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Hole, AN-2 Flex, 1/4" Stud, Short Barrel, Nickel Plated

Features: Large Size Seamless Uninsulated Compression Terminal, Double thick Tongue, With Inspection Window, Finish: Nickel Plated

Product Details

General

Application	For use on: Type AN aircraft cable, extra flexible conductors and commercial(code) conductors, Applications include aircraft, industrials, hospitals, electric utilities, marine, computers, and other equipment subject to vibration or requiring dependable electrical Performance
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	41
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Sub Brand	Terminals, HYLUG
Trade Name	HYLUG™
Type	YAV-L, Ring Tongue
UPC	781810113660

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.53 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - Length Overall inch	1.72 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.69 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.35 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Flex G Size	2
Conductor - Copper Flex H Size	2
Conductor - Copper Flex I Size	2
Conductor - Copper Flex K Size	2
Conductor - Copper Flex M Size	2
Conductor - Copper Str Aircraft Size	AN 2
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)