



YAV3002M16

by Burndy
Catalog ID: YAV3002M16

Hylug Copper tubing Compression terminals,300 mm²,M16 Stud, 2 Holes,Tin Plated

Product Details

General

Die Index	22
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638156
UPC 12 Digit	7818106381566

Dimensions

Bolt Size	M16
Dimension - B Length inch	6.9 in
Dimension - L Length Overall mm	135 mm
Dimension - Length Overall inch	5.30 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	44.2 in
Dimension - Strip Length inch	1.38 in
Dimension - Z inch	0.67 in
Thickness - Pad	0.27 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 mm ² ,600 AWG
-----------------------------	------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)