

# YAV300F2M10

by Burndy  
Catalog ID: YAV300F2M10

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 300 mm, M10 Stud, 44.5 mm Spacing, Standard Barrel, 38 mm Wire Strip Length



## Product Details

### General

Die Index	22
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641040
UPC 12 Digit	7818106410400

### Dimensions

Bolt Size	M10
Dimension - B Length inch	1.45 in
Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.92 in
Dimension - N inch	0.28 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1.50 in
Dimension - Z inch	0.42 in
Thickness - Pad	0.27 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	300 mm <sup>2</sup> ,500 AWG
-----------------------------	------------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)