

YAV300F2M16

by Burndy
Catalog ID: YAV300F2M16

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 300 mm, M16 Stud, 44.5 mm Spacing, Standard Barrel, 38 mm Wire Strip Length



Product Details

General

Die Index	22
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641071
UPC 12 Digit	7818106410711

Dimensions

Bolt Size	M16
Dimension - B Length inch	1.45 in
Dimension - L Length Overall mm	138 mm
Dimension - Length Overall inch	5.42 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1.50 in
Dimension - Z inch	0.67 in
Thickness - Pad	0.27 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 mm ² ,500 AWG
-----------------------------	------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)