

YAV300FM10

by Burndy
Catalog ID: YAV300FM10

Compression terminal Hylug Copper tubing; 1 Hole; 300 mm2; M10 Stud;
Tin Plating



Product Details

General

Die Index	22
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810640265
UPC 12 Digit	7818106402655

Dimensions

Bolt Size	M12
Dimension - B Length inch	1.45 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.16 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1.50 in
Dimension - Z inch	0.42 in
Thickness - Pad	0.27 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 mm ² ,500 AWG
-----------------------------	------------------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)