

YAV300FM20

by Burndy
Catalog ID: YAV300FM20

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 300 mm, 20 mm Stud, 4.09 IN L, Compression, 22 Index, 38 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	22
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323366
UPC 12 Digit	7818103233666

Dimensions

Bolt Size	M20
Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.45 in
Dimension - Hole Size inch	0.83 in
Dimension - Hole Size mm	21 mm
Dimension - Inside Diameter inch	0.98 in
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1.50 in
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.27 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 mm²,500 AWG
-----------------------------	-----------------

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)